







## APPLICATION NOTES:

- PRINSCO GOLDLOK COUPLERS ARE USED TO CONNECT TWO LENGTHS OF PIPE. DAMAGED SECTIONS CAN BE REMOVED AND REPLACED USING TWO GOLDLOK WATERTIGHT COUPLERS (AS SHOWN ABOVE).
- GOLDLOK COUPLERS ARE USED WHEN A WATERTIGHT SEAL BETWEEN TWO PIPES IS DESIRED.
- GOLDLOK COUPLERS FEATURE AN INTEGRATED GASKET AND REINFORCING BANDS WITH A BELL - BELL CONNECTION TO PROVIDE A POSITIVE SEAL.

## NOTES:

- ALL PIPE SHALL BE INSTALLED IN ACCORDANCE WITH ASTM D2321 STANDARD PRACTICE FOR UNDERGROUND INSTALLATION OF FLEXIBLE THERMOPLASTIC SEWER PIPE, LATEST EDITION.
- PRINSCO GOLDLOK WATERTIGHT COUPLERS ARE AVAILABLE IN SIZES FROM 12" 60" (300 - 150 mm).

THIS DETAIL DEPICTS RECOMMENDED INSTALLATION PRACTICES AND IS NOT INTENDED TO SUPERSEDE ANY NATIONAL, STATE OR LOCAL SPECIFICATIONS. PRINSCO BEARS NO RESPONSIBILITY FOR ANY ALTERATIONS. REVISION AND/OR DEVIATION FROM THIS STANDARD DETAIL. PRINSCO HAS NOT PERFORMED ANY ENGINEERING OR DESIGN SERVICE FOR THIS PROJECT. THE DESIGN ENGINEER SHALL REVIEW THESE DETAILS PRIOR TO CONSTRUCTION TO VERIFY SUITABILITY. © PRINSCO, INC.



1717 16TH ST. NE WILLMAR, MN 56201 www.prinsco.com

| TITLE:                   | HDPE PIPE - PIPE REPAIR - |        |           |                 | REV: |
|--------------------------|---------------------------|--------|-----------|-----------------|------|
| SECTION REPLACED GOLDLOK |                           |        |           | LDLOK           | B    |
| DRAWN BY:                | TRA                       | DATE:  | 03-Jul-17 | DRAWING NUMBER: |      |
| SCALE:                   | NTS                       | SHEET: | 1 OF 1    | D-1-133         | 5    |